

# Product Data Sheet

## Luminy® LX175

**Revision date** 07 May 2019  
**Page** 1 of 3  
**Date previous version** 01 Sep 2017  
**Version & language** 6/0975 - EN  
**Product availability** Global  
**Product status** Commercial

**PRODUCT DATA SHEET**  
**LUMINY® LX175**

Interested in solutions for bioplastics? Please contact us at  
[www.total-corbion.com](http://www.total-corbion.com) [pla@total-corbion.com](mailto:pla@total-corbion.com)

### DESCRIPTION

PLA is a biobased polymer derived from natural resources and offers a significant reduction in carbon footprint compared to oil-based plastics. Luminy® LX175 is a high viscosity, low flow, amorphous, transparent PLA resin suitable for film extrusion, thermoforming or fiber spinning.

### TYPICAL PROPERTIES<sup>1</sup>

Physical properties	Method	Typical value
Density	Literature value	1.24 g/cm <sup>3</sup>
Melt flow index	ISO 1133-A (210°C/2.16kg)	6 g/10 min
Melt flow index	ISO 1133-A (190°C/2.16kg)	3 g/10 min
Stereochemical purity	Total Corbion PLA method	96% (L-isomer)
Appearance	Visual	Crystalline white pellets
Residual monomer	Total Corbion PLA method	≤ 0.3%
Water / moisture	Coulometric Karl-Fischer	≤ 400 ppm
Melting temperature	DSC	155°C
Glass transition temperature	DSC	60°C
Mechanical properties	Method	Typical value
Tensile modulus	ISO 527-1	3500 MPa
Tensile strength	ISO 527-1	45 MPa
Elongation at break	ISO 527-1	≤ 5%
Charpy notched impact, 23°C	ISO 179-1eA	≤ 5 kJ/m <sup>2</sup>
Heat deflection temp., amorphous <sup>2</sup>	ISO 75-1	60°C

<sup>1</sup> Typical properties, not to be interpreted as specifications  
<sup>2</sup> HDT B, 0.45MPa flatwise. HDT depends on processing conditions.

### PROCESSING INFORMATION & RECOMMENDATIONS

Standard PLA can be processed on conventional extrusion equipment and can be used as neat resin or as part of a compound to further optimize overall material properties. It is recommended to use a general purpose screw with L/D ratios between 24 and 32. Pre-drying of the resin is recommended.

#### Start-up and shutdown

1. Purge the system with a polyolefin or a purging compound (e.g. Dyna-Purge, Clean LDPE) at its recommended temperature settings.
2. Reset the temperature settings to the recommended PLA temperature profile.
3. Purge with PLA resin or PLA compound until stable processing is obtained free of contaminants.
4. Reset the temperature settings to the recommended purging compound temperature profile.
5. Purge with a polyolefin or a purging compound for 5 times the average residence time.

After completion of the run, PLA must be removed from the whole system. PLA can degrade into lactic acid causing corrosion of the equipment (e.g. die plates).

#### Processing recommendations

Predrying	4-6 hours at 85°C
Feed zone	20-40°C
Melt zone	170-190°C
Mixing & conveying	190-210°C
Die head temperature	190-210°C

*Typical settings, may require optimization*



© Copyright 2019 Total Corbion PLA. All rights reserved. No part of this publication may be copied, downloaded, reproduced, stored in a retrieval system or transmitted in any form by any means, electronic, mechanical, photocopied, recorded or otherwise, without permission of the publisher. No representation or warranty is made as to the truth or accuracy of any data, information or opinions contained herein or as to their suitability for any purpose, condition or application. None of the data, information or opinions herein may be relied upon for any purpose or reason. Total Corbion PLA disclaims any liability, damages, losses or other consequences suffered or incurred in connection with the use of the data, information or opinions contained herein. In addition, nothing contained herein shall be construed as a recommendation to use any products in conflict with existing patents covering any material or its use. TOTAL is a trademark owned and registered by Total S.A., used under license by Total Corbion PLA BV. CORBION is a trademark owned and registered by CORBION N.V. used under license by Total Corbion PLA BV.

# Product Data Sheet

## Luminy® LX175

**Revision date** 07 May 2019  
**Page** 2 of 3  
**Version & language** 6/0975 - EN

### MOISTURE & PRE-DRYING

It is recommended to dry Luminy® LX175 from the packaging for 4-6 hours at 85°C. Drying of standard PLA can be performed in a desiccant hot air dryer, with a dew point of -40°C or less. It is recommended to reduce the moisture content before melt processing to a level less than 250ppm and preferably less than 100 ppm, measured by e.g. Karl-Fischer or Brabender aquatrac method. Predrying is in particular important prior to injection molding, film and sheet production. Moisture causes hydrolysis of the PLA polymer during melt processing, resulting in reduced mechanical performance in the final part.

### PACKAGING & STORAGE CONDITIONS

Luminy® LX175 is available in 1250 kg form-stable aluminum-lined big bags and 25 kg sample bags (moisture level not guaranteed for sample bags). It is recommended to store PLA polymer in its closed, original moisture-barrier packaging at temperatures below 50°C. Storage in direct sunlight should be avoided. The supplied PLA polymer pellets are typically semi-crystalline, unless otherwise stated.

### COMPOSTABILITY

Composting of organic waste helps to divert organic waste from landfill or incineration. Composting is a biological process in which organic wastes are degraded by microorganisms into carbon dioxide, water and humus, a soil nutrient. Luminy® PLA polymers are in compliance with the EN-13432 standard. Luminy® LX175 has been certified compostable by TUV Austria (OK Compost S478) and by European Bioplastics (Seedling 7W2030) up to a thickness of 3.5 mm. As the compostability of the end product is also dependent on the geometry of product, it is the responsibility of the manufacturer of the end product to ensure compliance with the regulations.



### BIOBASED CONTENT

Luminy® LX175 has a biobased content of 100% (confidence level 1) and a biobased carbon content of 100% according to EN16785-1 under certificate number DIC-00001. Luminy® LX175 is certified 100% biobased according to ASTM D6866 under the USDA Biopreferred program.



### FOOD CONTACT STATUS

In the European Union, Luminy® PLA polymers are compliant with EU commission regulation 10/2011 of 14 January 2011 (and amendments) on plastic materials and articles intended to come into contact with food. Lactic acid is considered a dual use substance, since lactic acid is approved as a food additive (additive number E270). There are no SMLs or SML(T)s for the ingredients used to produce Luminy® PLA. The regulation does include a migration limit of 10 mg/dm<sup>2</sup> on the overall migration from finished plastic articles into food. It is the responsibility of the manufacturer of the final product, when intended as a food contact product, to determine that the use of the product is safe and also suitable for the intended application. While it is Total Corbion PLA's conclusion that the above mentioned polymers are permitted, it is the final product which must meet the given regulations and the manufacturer should take responsibility to check if the final product is in compliance with these regulations.

In the United States of America, Luminy® PLA as supplied by Total Corbion PLA has been evaluated and was found to be suitable for use in food contact applications. On 30 November 2018, FCN 001926 as applied for by Total Corbion PLA to the FDA became effective. It is included in the list of effective notifications for FCNs on the website of the FDA. The evaluation performed was in line with the requirements of Section 201(s) and Section 409 of the Federal, Drug and Cosmetic Act, and Parts 182, 184 and 186 of the Food Additive Regulations. Luminy® PLA neat resin is approved for all food types and conditions of use B through H.



© Copyright 2019 Total Corbion PLA. All rights reserved. No part of this publication may be copied, downloaded, reproduced, stored in a retrieval system or transmitted in any form by any means, electronic, mechanical, photocopied, recorded or otherwise, without permission of the publisher. No representation or warranty is made as to the truth or accuracy of any data, information or opinions contained herein or as to their suitability for any purpose, condition or application. None of the data, information or opinions herein may be relied upon for any purpose or reason. Total Corbion PLA disclaims any liability, damages, losses or other consequences suffered or incurred in connection with the use of the data, information or opinions contained herein. In addition, nothing contained herein shall be construed as a recommendation to use any products in conflict with existing patents covering any material or its use. TOTAL is a trademark owned and registered by Total S.A., used under license by Total Corbion PLA BV. CORBION is a trademark owned and registered by CORBION N.V. used under license by Total Corbion PLA BV.

# Product Data Sheet

## Luminy® LX175

**Revision date** 07 May 2019  
**Page** 3 of 3  
**Version & language** 6/0975 - EN

### NOTICE REGARDING USE RESTRICTIONS

Unless specifically agreed to in writing, Total Corbion PLA will not knowingly market any product into any of the following commercial or developmental applications: (1) bottles or preforms, unless specific arrangements on recycling and end-of-life are in place, (2) microbeads used in personal care products, including without limitation, cosmetics or over-the-counter drugs, (3) components of products intended for human or animal consumption or (4) any application that is intended to be used inside the human body.



© Copyright 2019 Total Corbion PLA. All rights reserved. No part of this publication may be copied, downloaded, reproduced, stored in a retrieval system or transmitted in any form by any means, electronic, mechanical, photocopying, recorded or otherwise, without permission of the publisher. No representation or warranty is made as to the truth or accuracy of any data, information or opinions contained herein or as to their suitability for any purpose, condition or application. None of the data, information or opinions herein may be relied upon for any purpose or reason. Total Corbion PLA disclaims any liability, damages, losses or other consequences suffered or incurred in connection with the use of the data, information or opinions contained herein. In addition, nothing contained herein shall be construed as a recommendation to use any products in conflict with existing patents covering any material or its use. TOTAL is a trademark owned and registered by Total S.A., used under license by Total Corbion PLA BV. CORBION is a trademark owned and registered by CORBION N.V. used under license by Total Corbion PLA BV.